

Impulsní relé, tlačítko, 230 V~, 2zap. kont.



Typ **Z-S230/SS**
 Catalog No. **265271**

Ověření návrhu podle ČSN EN 61439

Technické údaje pro ověření konstrukce		
Provozní teplota okolí min.	°C	-20
Provozní teplota okolí max.	°C	45

Technická data podle ETIM 6.0

Devices for distribution board-/surface mounting (EG000062) / Latching relay (EC000188)		
Electric engineering, automation, process control engineering / Electrical installation, device / Modular serial built-in device for electrical circuit distributors / Latching relay for distribution board (ec1@ss8.1-27-14-23-06 [AFZ818012])		
Function		Mechanical switch
Mounting method		DIN rail
Width in number of modular spacings		1
Built-in depth	mm	60
Number of normally open contacts		2
Number of normally closed contacts		0
Number of change-over contacts		0
Control voltage 1	V	230 - 230
Type of control voltage 1		AC
Frequency control voltage 1	Hz	50 - 50
Control voltage 2	V	0 - 0
Type of control voltage 2		AC
Frequency control voltage 2	Hz	0 - 0
Rated switch current	A	32
Supply voltage	V	250 - 250
Voltage type of supply voltage		AC
Max. incandescent lamp load	W	0
Max. load fluorescent lamp	VA	0
Max. load fluorescent lamp (Duo circuit)	VA	0
Max. load fluorescent lamp (parallel compensated)	VA	0
Max. switching current (cos phi = 0.6)	A	0
Manual operation possible		Yes

Rozměry

