



Main

Transformer type	Safety transformer
Range of product	DuoLine
Device short name	TR'clac

Complementary

[Ue] rated operational voltage	230 V AC 50/60 Hz
Output voltage	12/24 V: +/-5 % on load
Output short-circuit protection	Built-in
Rated power in VA	25 VA
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	10
Height	89 mm
Width	90 mm
Depth	60 mm
Auxiliary connection terminal	Tunnel type terminals <= 4 mm ²

Environment

Standards	EN 60742
Product certifications	NF
Ambient air temperature for operation	-20...50 °C

Contractual warranty

Period	18 months
--------	-----------