

# 90° connection plate VABF-S4-1-A2G2-G14

Part number: 539721

FESTO

For valve terminals VTSA and VTSA-F, working lines 2 and 4, at a 90° angle.



## Data sheet

Feature	Value
Width	26 mm
Based on the standard	ISO 15407-2
Assembly position	Any
Operating pressure	-0.9 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
Protection class	IP65 NEMA 4
Ambient temperature	-5 ... 50 °C
Product weight	217 g
Mounting type	with through hole
Material housing	Aluminium die cast