

## 7 XL 10

### Combination spanner

extra long

Code	ETIM
<b>6097300</b>	<b>EC002176</b>
EAN	UNSPSC
<b>4010886609736</b>	<b>27-11-17-13</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-01-05</b>
Customs tariff number	
<b>82041100</b>	



### Article description

- Extra long shaft for deep range of use and more torque
- Chrome-vanadium steel 31CrV3, chrome-plated
- Carefully forged and professionally machined
- Overloading indicated by deformation
- Secure grip thanks to hollow shaft - very ergonomic and handy
- Glare-free look due to matt chrome
- Designed for universal use
- Top-grade industrial quality for the hardest of continuous use
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Ring: 15° offset from shaft, with UD profile for gentle transmission of force

### Article information

Contents (Qty of pieces)	1	Width of head 2 [mm]	24 mm
Net weight [kg]	0,06 kg	Head height 2 [mm]	5 mm
Total length [mm]	190 mm	Head height 1 [mm]	8,5 mm
Total width [mm]	23 mm	Width of head 1 [mm]	16,0 mm
Total height [mm]	12 mm	Mouth position 1	15°
Surface	chrome-plated	Ring profile	UNIT-DRIVE
Material	31CrV3	Weight	0,020 lbs
Standard	similar to DIN 3113 - form A ISO 3318 ISO 7738	Ring angle	15°
Width across flats 1 [mm]	10		