

**Technical Data**

Material : Polyester  
 Colour : black  
 Operating temperature : -50 °C to +150 °C  
 Intermittent temperature : 220 °C  
 Melting point : 250 °C  
 Flammability : self extinguishing according to UL94V2  
 : according FMVSS 302 (Type B)  
 Certification : DIN EN 45545:2013  
 : UL File E197993



TYPE	Recommended Application Diameter		Surface Coverage app. in %	Weight [g/m]
	min. [mm]	max. [mm]		
HEGPX03	2	6	64	530
HEGPX06	3	10	78	840
HEGPX09	5	16	71	1320
HEGPX12	6	19	77	1732
HEGPX20	13	32	77	2280
HEGPX30	19	45	71	3220
HEGPX40	32	70	79	4880
HEGPX50	38	76	80	5920