

Professionally approved products.

Datasheet

Crimp Tool for Coaxial Connectors

RS Stock number: 447-459



Specifications:

- Non slip main handle and low friction moving handle ensure a comfortable hand grip
- Provides two-hand grip in the final phase of crimping, increasing comfort and productivity
- Full cycle crimp mechanism to ensure consistent, reliable crimp
- Ratchet release mechanism to clear mis-crimps and obstructions
- Precision eccentric adjustment for consistent performance and ability to calibrate
- Each tool has a unique serial number for traceability
- Durable: life span exceeds 50,000 cycles
- High strength, through hardened alloy Swedish steel construction

Crimp nest:	3.25 mm / .128"
	4.52 mm / .178"
	1.69 mm / .067"
Wire size:	RG122/U, RG174A/U, RG179B/U, RG180B/U, RG187A/U, RG188A/U, RG279/U, RG303/U, RG316/U
Connector:	Coaxial connector
Description:	For example SMA, SMB, SMC on RG 174, RG 179.
Crimp profile:	Hexagon
Length:	195 mm/7.68"
Width:	18 mm/0.71"
Height:	59 mm/2.32"
Weight:	350 g/0.75 lb
Life span, cycles:	50,000