
E-200 CASSIOPEIA POCKET PC 2002



Technical Specs

Processor	Intel Strong Arm 1110 206MHz
OS	Pocket PC 2002
RAM	32MB Flash ROM--64MB RAM
Processor Cache	16KB
Data Cache	8KB
Display	Reflective TFT color LCD 65,536 colors Screen Size Diag: 3.5 inch Screen Resolution: 240 x 320 Dot Pitch: .22mm
Battery Life	Up to 12 hours. Extended time with Optional Combination PC Card Adapter/Auxiliary Power Unit
Card Slots	SD/MMC slot CF card slot (TYPE II) Optional Combination PC Card Adapter/Auxiliary Power Unit (via 32pin) includes rechargeable battery
Wireless Communication	-Optional CF Card Wireless Modem -Optional PC Card Wireless Modem (Requires Optional Combination PC Card Adapter/Auxiliary Power Unit) -Optional Cable to Cell Phone Adapter (available for select phones)
Interfaces	Serial RS232C USB Client (via cradle of cable) USB Host (via cradle)
Infrared	IrDA Ver1.2 IrDa Speed: 115kbps
Audio	Stereo headphone jack Built-in Speaker Built-in Microphone
Power	Li-ion rechargeable replaceable battery (950 mAh) Backup Battery Type: CR-2032
Approximate Size	5 1/8"(L) x 3 3/16"(W) x 11/16"(H)
Weight	Approximately 190g/6.7oz.

Included: E-200, Stylus, Softcase, Main Battery, Backup Battery, AC Adaptor with AC cable, USB Cradle, CASIO CD-ROM, MS CD-ROM, QS Guide, EULA Card, CD ReadME, Registration/Warranty Card, Tourist Warrant Card, Accessory Form, PCMagazine Insert