## **I4COUPLUSB3IP68**

IP68 USB 3.0 COUPLER

## **BENEFITS**

- IP 68
- IP68 protection level suitable to harsh environments: dustproof & waterproof
- USB 3.0 type A-A connector
- 1/4 turn waterproof lock







### **DESCRIPTION / APPLICATIONS -**

- USB 3.0 coupler, female type A to female type A
- Allows existing USB waterproof link extension
- Suitable to harsh environments (industrial, outdoor, ...)
- IP68 protection rating

#### NORMS —

Universal Serial Bus 3.0 specification

USB Type-A connector

#### **ENVIRONMENTAL PROPERTIES —**

#### **OPERATING TEMPERATURE:**

-25°C to +50°C

#### **CONFORME:**

RoHS and REACH







## **DATA SHEET**

FT1 04/03/2021 FR

## **ELECTRICAL PROPERTIES**

**CURRENT:** 

25 mA

**CONTACT RESISTANCE:** 

 $10 \text{ m}\Omega$ 

**INSULATION RESISTANCE:** 

100 MΩ

**DIELECTRIC WITHSTAND VOLTAGE:** 

100V

**OPERATIONAL VOLTAGE:** 

30V

## MECHANICAL / TECHNICAL PROPERTIES -

COATING:

Plastic ring : PA 66 Connector : Zn+Ni alloy **INSERTION CYCLE:** 750 cycles

### PERFORMANCES -

SYSTEM

USB 3 Type A

APPLICATION

USB 3 up to 7.5GHz

### **DRAWINGS**
















# DATA SHEET

FT1 04/03/2021 FR

## **ORDER INFORMATION**

P/N	DESCRIPTION	PACKAGING
I4COUPLUSB3IP68	IP68 USB 3.0 coupler	Unit

## **ASSOCIATED PRODUCTS**



**I4USB3IP68**IP68 Plug USB 3.0



**I4CAPPLUG** IP68 coupler or connector cap