



# one-way flow control valve CRGRLA-M5-B

Part number: 161403

FESTO

Corrosion resistant,  
with swivel joint and female thread.



## Data sheet

Feature	Value
Valve function	One-way flow control function
Pneumatic connection, port 1	M5
Pneumatic connection, port 2	M5
Adjusting element	Slotted head screw
Mounting type	Threaded
Standard nominal flow rate in flow control direction	95 l/min
Standard nominal flow rate in non-return direction	77 ... 95 l/min
Operating pressure	0.2 ... 10 bar
Ambient temperature	-20 ... 80 °C
Maritime classification	see certificate
Assembly position	Any
Standard flow rate in direction of flow control: 6 -> 0 bar	165 l/min
Standard flow rate in blocked direction: 6 -> 0 bar	140 ... 150 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Storage temperature	-10 ... 40 °C
Food-safe	See Supplementary material information
Medium temperature	-10 ... 60 °C
Nominal size	2 mm
Max. tightening torque	1.5 Nm
Permissible actuation moment, regulating screw	0.2 Nm
Product weight	10.2 g
Materials note	Conforms to RoHS
Material seals	FPM PVC
Material hollow bolt	High alloy steel
Material adjusting screw	High alloy steel, non-corrosive
Material swivel fitting	High alloy steel, non-corrosive