


P1,P2: M-Y139C
M-139H
P3: M-426E

Customer No: _____



P1		P2	
2	—————	3	BROWN
3	—————	2	RED
4	—————	6	ORANGE
5	—————	5	YELLOW
6	—————	4	GREEN
7	—————	8	BLUE
8	—————	7	BLACK
SHIELD	—————	SHIELD	



*NOTE: ALL relevant materials are complied with RoHS directive

4	BLACK PVC TUBE ϕ 3.0*22mm	2	M304
	ALUMINUM FOIL 33*65mm	2	M579
	MOLDED PE COLOR TRANSPARENT		M280
	MOLDED PVC GREY		M304
3	NON-UL 7C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 4.0mm, JACKET GREY, DRAWING No. EMAL2807C-040	L-20mm	M304
2	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, GREY	4	M95
1	DB9 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	2	M108
No.	DESCRIPTION	Q'TY	Supplier

APPROVED		SL-915	Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm
CHECKED			
DRAWING			
DATE	ITEM NO.		
		UNIT:mm	