

DIN rail perforated - NS 32 PERF 2000MM - 1201002

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




G-profile DIN rail, material: Steel, perforated, height 15 mm, width 32 mm, length 2 m

Why buy this product



Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 017132
Weight per Piece (excluding packing)	1380.0 g
Custom tariff number	72166190
Country of origin	Germany

Technical data

Dimensions

Height	15 mm
Length	2000 mm
Width	32 mm

General

Material	Steel
Coating	Galvanized, passivated with a thick layer
Color	silver
Nominal current I_N	4200 A

Classifications

eCl@ss

eCl@ss 4.0	27110804
------------	----------

DIN rail perforated - NS 32 PERF 2000MM - 1201002

Classifications

eCl@ss

eCl@ss 4.1	27110804
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27400602
eCl@ss 7.0	27400602
eCl@ss 8.0	27400602

ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Drawings

Dimensional drawing

