

## FEATURES

- Colour: black
- Flammability rating: UL94V-0
- Output connector: 2.1mm x 5.5mm x 12mm
- Linear Power Supply

## RS PRO, 14W Plug In Power Supply 24V ac, 580mA, Level VI Efficiency, 1 Output Linear Power Supply, Type C

RS Stock No.: 139-1773



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

**Product Description ATTRIBUTE 1**

From RS PRO, comes a high quality 14W linear plug-in power supply. This linear power adapter is an excellent plug in power solution as it is cost effective, highly reliable and designed for use in Europe. As part of our RS Pro line of power adapters, you are ensured a reliable & robust power solution.

**General Specifications**

Type	Linear Power Supply
Plug Type	Type C
Output Connector	2.1mm x 5.5mm x 12mm
Input Connector	EU Plug
Number Of Outputs	1
Energy Efficiency Level	VI
Applications	Fans, Radios, Video, Toys, Aquariums, Desk lamps and LED lamps

**Electrical Specifications**

Output Voltage	24V ac
Input Voltage	230 V ac, 240 V ac
Output Current	580mA
Power Rating	14W
Load Regulation	±5%
Leakage Current	0.25mA max. @ 264VAC, 50Hz
MTBF	50,000 hours (25°C)
Load Regulation	+/-5%
Short Circuit	Yes

**Mechanical Specifications**

<b>Cable Length</b>	1.8m
<b>Width</b>	60mm
<b>Length</b>	89mm
<b>Depth</b>	61mm
<b>Humidity</b>	30% - 85% R.H.

**Operation Environment Specifications**

<b>Maximum Temperature</b>	40°C
<b>Minimum Temperature</b>	-20°C

**Approvals**

<b>Compliance/Certifications</b>	EN61558, IEC61000-4-2/ESD, IEC61000-4-3, IEC61000-4-4/EFT, IEC61000-4-5/SURGE, IEC61000-4-6/CS
<b>Standards Met</b>	IEC, UL



