



12V XR Brushless 14mm SDS-Plus Hammer Drill (2 x 3 Ah)

DCH072L2-QW

12V XR power tool battery platform for extra long run time and the convenience of rechargeable power tool batteries

Brushless motor provides improved runtime and durability
Compact, lightweight and ergonomic design for improved comfort and support during extended operating periods

Bright white LED with delay feature improves visibility
1.19 of impact energy, 0-4280 bpm with a no load speed of 0-910 rpm, ideal for drilling anchors and fixing holes into concrete, brick and masonry from 4mm to 14mm



Power Source	Cordless
--------------	----------

No Load Speed	910 Rpm
---------------	---------

Impact energy (EPTA 05/2009)	1.1000000000000001 J
------------------------------	----------------------

Max. Drilling Capacity (Wood)	13 mm
-------------------------------	-------

Max. Drilling Capacity (Metal)	10 mm
--------------------------------	-------

Max. Drilling Capacity (Concrete)	14 mm
-----------------------------------	-------