

Datasheet

Stock No: 125-4387

RS Pro Surface Mount Interlocked Socket With RCD 3P+N+E IP44 16A 400V



RS Pro surface mount RCD protected interlocked sockets feature a hard plastic housing, a padlockable interlock switch and a colour coded terminal cap. This range features screw terminals for safe and reliable electrical connections. They are designed for industrial use, but are also suitable for commercial environments.

Specifications:

Rated current:	16A
Poles:	3P+N+E
Rated voltage:	400V
Working Frequency:	50Hz
Working Frequency:	60Hz
Colour:	Red
Protection degree:	IP44
Cable Outlet:	M25 x 1.5