

FEATURES

- **Heavy Duty Design:** Provides robust support for large cable bundles, ensuring stability and security.
- **High Tensile Strength:** Withstands up to 114 kg, offering excellent resistance to breakage under tension.
- **UL 94 V-2 Fire Behaviour:** Meets safety standards for flammability, enhancing safety in environments where fire resistance is crucial.
- **Wide Operating Temperature Range:** Suitable for use in environments up to 85 °C, allowing for versatile application in various conditions.
- **Nylon Material:** Offers durability and resistance to wear, ensuring long-lasting performance.
- **Large Bundle Capacity:** Accommodates bundles up to 312 mm in diameter, making it suitable for extensive cabling needs.

RS PRO Heavy Duty Cable Tie, 1030 mm Length

RS Stock No: 656-113



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO heavy duty cable tie is designed for securing and organising large bundles of cables or wires. Made from durable nylon, it offers a reliable solution for managing cables in industrial settings. With a maximum bundle diameter of 312 mm, it is ideal for heavy-duty applications where strength and durability are paramount.

General Specifications

Colour	Natural
Product Type	Cable Tie
Sub Type	Heavy Duty Cable Tie
Tensile Strength	114 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	No

Mechanical Specifications

Length	1030 mm
Material	Nylon
Maximum Bundle Diameter	312 mm
Width	12.7 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, CE 40022513, cULus E97527, DNV TAE00000US, LR 16-80006, RoHS, UL94V-2, VDE 40022513
---------------------	---