



Ring ratchet insert adaptor 717

717



Product no. **58170112**
GTIN **4018754348411**
Model **717/12**



Label.

Ring ratchet insert adaptor 12mm Tool holders 9 x 12

Product highlights.



PRODUCT IMAGE
IN PROGRESS

Fine-tooth ring ratchet.

The high level of accuracy is achieved by flat transducers and a special technology for immediate data processing directly in the transducer. Thanks to an integrated measurement amplifier, the testing device is resistant to bending moments and transverse forces.



PRODUCT IMAGE
IN PROGRESS

For confined spaces.

This ring ratchet insert adaptor enables precise work with a working angle of just 5°. Thanks to its slim design, it is particularly well-suited for use in tight and hard-to-reach areas where larger movements are not possible.



PRODUCT IMAGE
IN PROGRESS

Safe switching.

The high level of accuracy is achieved by flat transducers and a special technology for immediate data processing directly in the transducer. Thanks to an integrated measurement amplifier, the testing device is resistant to bending moments and transverse forces.



PRODUCT IMAGE
IN PROGRESS

Safe and durable.

The high level of accuracy is achieved by flat transducers and a special technology for immediate data processing directly in the transducer. Thanks to an integrated measurement amplifier, the testing device is resistant to bending moments and transverse forces.


Technologies and features.



High Performance Quality (HPQ®)

Our HPQ® tool is made of wear-resistant high-performance steel, yet is thin-walled and lightweight. It withstands high torques and is ideal for work in confined spaces such as turbines.

Technical drawing.



Technical attributes.

Number of teeth	72
Working angle	5 °
Width mm (b)	25 mm
Size square socket [internal square drive]	9 x 12 mm
Height mm (h)	9,1 mm
Alloy	HPQ® high performance steel
max. torque	89 N·m
S	42 mm
Width across flats [mm]	12 mm

Logistics data.

Depth mm (IFS)	70
Width mm (IFS)	25
Height mm (IFS)	19
WEEE/ElektroG	nicht ear-pflichtig
Length (packed, mm)	78
Width (packed, mm)	34
Height (packed, mm)	21
Volume (packed, dm3)	0.055692 dm3
Art. no.	58170112
Weight (gross, kg)	0,092
Weight PAP (kg)	0,000
Weight PVC (kg)	0,002
GTIN	4018754348411
Country of origin AWR	CHINA
Region of origin	Ausländischer Ursprung
Customs tariff no.	82042000
Packing standard	1
Weight	90 g

Variants.

Art. no.	Model no. (ERP)	Description	GTIN
58170108	717/8	Ring ratchet insert adaptor 8mm Tool holders9 x 12	4018754348619
58170110	717/10	Ring ratchet insert adaptor 10mm Tool holders9 x 12	4018754348626
58170112	717/12	Ring ratchet insert adaptor 12mm Tool holders9 x 12	4018754348411
58170113	717/13	Ring ratchet insert adaptor 13mm Tool holders9 x 12	4018754348428
58170117	717/17	Ring ratchet insert adaptor 17mm Tool holders9 x 12	4018754348435
58170119	717/19	Ring ratchet insert adaptor 19mm Tool holders9 x 12	4018754348442
58170122	717/22	Ring ratchet insert adaptor 22mm Tool holders9 x 12	4018754348510

GTIN.



Images.



STAHLWILLE Eduard Wille GmbH & Co. KG

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0 · Fax: +49 202 4791-393

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH & Co. KG, Wuppertal