

8937

Max. 18 W

AC/DC POWER SUPPLIES - LINEAR - REGULATED

- Trinnløs justerbar utgangsspenning
- Sekundærsvitsjet
- Termosikring i transformator
- Nettledning
- Sekundærledning eller snappkontakt
- Kan leveres med festebrakett
- Stepless adjustable output voltage
- Secondary switch
- Thermal fuse in transformer
- Mains cord
- Cable or snap terminals
- Mounting bracket available



Tekniske data	Technical specifications	
Inngangsspenning:	<i>Input voltage:</i>	230 VAC +6/-10%, 50/60Hz
Utgangsspenning:	<i>Output voltage:</i>	5-24 VDC
Maks. utgangseffekt:	<i>Max. output power:</i>	18 W
Maks. laststrøm	<i>Max. load current:</i>	2,0 A
Lastregulering:	<i>Load regulation:</i>	2,0%
Linjeregulering:	<i>Line regulation:</i>	0,1%
Svitsjefrekvens:	<i>Switch frequency:</i>	33 kHz
Temperaturområde:	<i>Temperature range:</i>	-10°C - +40°C
Rippel:	<i>Ripple:</i>	10 mV RMS
Strømbegrensning:	<i>Current limiting:</i>	2,5 A *
Isolasjonsklasse:	<i>Insulation class:</i>	II
Isolasjonsspenning:	<i>Insulation voltage:</i>	3000 VAC
Elektrisk sikkerhetsstandard:	<i>Electrical safety standard:</i>	EN 60065, EN 60950
EMC standarder	<i>EMC standards</i>	
• Emisjon:	• <i>Emission:</i>	EN 50081-1, EN 60555
• Immunitet:	• <i>Immunity:</i>	EN 50082-1
Mål (LxBxH):	<i>Dimensions (LxWxH):</i>	98 x 108 x 55 mm
Vekt:	<i>Weight:</i>	1,0 kg
* Strømbegrensning er innvendig justerbar.		
* <i>Current limiting is internally adjustable.</i>		