

Finishing Sander LXT®

DBO481Z

18V • 112 x 102 mm

LXT® Battery powered Finishing Sander for demanding use.

Compact and lightweight structure and conveniently located on/off switch for easy one handed operation. Compatible with various pads.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	22000 / 28000 min ⁻¹
Vibrations per minute	11000 / 14000 min ⁻¹
Orbits per Minute	11000 - 14000 min ⁻¹
Sanding Pad Dimensions	112 x 102 mm
Dimensions of Clamped Abrasive Sheet	114 x 140 mm
Pad size (triangle)	94 x 94 mm
Sanding Orbit Diameter	1,5 mm
Sound Pressure Level (L _{pA})	75 dB(A)
Product net weight	1,1 kg
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,4 - 1,7 kg

User benefits

- Electric brake for maximum productivity and increased operator safety
- Compatible with various pads
- Large clamping lever for quick and easy paper installation
- Efficient through-the-pad dust collection system for a cleaner work environment

EAN 0088381760805

Link to product - www.makitauk.com



Related products

Standard AC

166078-4

Dust Bag



257202-1

Ring 25, Bo4555



450066-4

Hole Punch Plate



Optional AC

135246-0

Dust Box + Paper dust bag 1 pc



191Y22-2

Triangular Base Plate for DBO480 &



191Y23-0

Rectangular Base Plate Complete



191Y24-8

Base Plate



191Y25-6

Square pad (clamp)



450066-4

Hole Punch Plate



794296-0

Abrasive Paper Set



Other

User manual

Parts drawing