




SWITCHING POWER SUPPLY

線材規格圖
WIRING HARNESS

DOC No	FB-1U-CI10	REV	A0
Date	2004.12.07	UNIT	mm
P/N	WU2224-450AW		




AWG	#16	#18	#20	#22	#24	#26
D	<1.8	<1.8	<1.5	<1.2	<1.0	<1.0

- TWISTED
- TWISTED & HALF TIN DIPPED
- TWISTED & FULL TIN DIPPED

MODEL

Tolerance

CUSTOMER



22P#1

1	UL1007	AWG18	ORANGE	+3V3	24P #1-P1
2	UL1007	AWG18	ORANGE	+3V3	24P #1-P13
3	UL1007	AWG18	ORANGE	+3V3	24P #1-P12
4	UL1007	AWG20	GRAY	P.G.	24P #1-P8
5	UL1007	AWG20	GREEN	PS_ON	24P #1-P16
6	UL1007	AWG26	BLACK	GND	24P #1-P3
7	UL1007	AWG20	RED	+5V	24P #1-P6
7	UL1007	AWG20	RED	+5V	24P #1-P4
8	UL1007	AWG18	BLACK	GND	24P #1-P5
9	UL1007	AWG18	BLACK	GND	24P #1-P7
10	UL1007	AWG20	BLUE	-12V	24P #1-P14
11	UL1007	AWG18	YELLOW	+12V1	24P #1-P11
12	UL1007	AWG20	BLACK	GND	24P #1-P3
13	UL1007	AWG20	PURPLE	+5Vsb	24P #1-P9
14	UL1007	AWG20	ORANGE	+3V3	24P #1-P2
15	UL1007	AWG26	ORANGE	+3V3s	24P #1-P2
16	UL1007	AWG18	RED	+5V	24P #1-P21
17	UL1007	AWG20	RED	+5V	24P #1-P22
17	UL1007	AWG20	RED	+5V	24P #1-P23
18	UL1007	AWG18	BLACK	GND	24P #1-P17
19	UL1007	AWG18	BLACK	GND	24P #1-P15
20	UL1007	AWG20	BLACK	GND	24P #1-P19
20	UL1007	AWG20	BLACK	GND	24P #1-P18
21	UL1007	AWG18	YELLOW	+12V	24P #1-P10
22	UL1007	AWG18	BLACK	GND	24P #1-P24