


NO	DESCRIPTION	DATE
△	BACKGROUND FORMAT UPDATED	01.21.10'
△	DEL PROOF VOLTAGE WORKING VOLTAGE VOLTAGE RATING 60 → 85	12.31.14'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-1 GHz
- 1.2 NOMINAL IMPEDANCE: 50 OHM
- 1.3 VOLTAGE RATING: 335 VOLTS MAX. △

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- 2.4 CRIMP FERRULE: BRASS PER JIS-C2700

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

- 4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A
- 4.2 CABLE RETENTION 15 lbs MIN.

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -40° C TO +85° C △

APPROVED

by _____ DATE: _____



DESCRIPTION		SMA PLUG CRIMP ST.+SMA PLUG CRIMP ST.+RG-174U						
製圖	DRAWN	TOLERANCE	品名	YH47-08	日期	DATE	版次	REV.
	<i>Kristina</i>							
檢圖	CHECK	TOLERANCE	品名	YH47-08	日期	DATE	版次	REV.
	<i>Jenny</i>							
認定	APPROVAL	TOLERANCE	品名	YH47-08	日期	DATE	版次	REV.
	<i>Jenny</i>							
		ANGLE						

NO	DESCRIPTION	Q'TY	FINISH
3	HEAT SHRINK TUBE	2	BLACK
2	CABLE	1	RG/174U
1	19-03-3 174U(50Ω)	2	T.G.G