

FEATURES

- **UV Resistant:** Provides long-lasting performance in outdoor environments.
- **High Tensile Strength:** Supports up to 80 kg, ensuring robust cable management.
- **Fire Behaviour UL 94 V-2:** Offers flame retardant properties for enhanced safety.
- **Wide Operating Temperature Range:** Suitable for use up to 85 °C, accommodating various environmental conditions.
- **Large Bundle Diameter:** Accommodates bundles up to 275 mm, ideal for large cable assemblies.
- **Durable Nylon Material:** Ensures longevity and resistance to wear and tear.

RS PRO Heavy Duty Cable Tie, 914 mm Nylon

RS Stock No: 656-069



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO Heavy Duty Cable Tie is designed for secure and reliable bundling of cables and wires. Made from durable nylon, this cable tie is ideal for heavy-duty applications where strength and UV resistance are crucial. With a maximum bundle diameter of 275 mm, it ensures a firm hold in various industrial settings.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Heavy Duty Cable Tie
Tensile Strength	80 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	914 mm
Material	Nylon
Maximum Bundle Diameter	275 mm
Width	9 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, CE 40022513, cULus E97527, DNV TAE00000US, LR 16-80006, RoHS, UL94V-2, VDE 40022513
---------------------	---