

M18 MDTL-O

M18™ MULTI-DIRECTIONAL TASK LIGHT

- TRUEVIEW™ high definition lighting with up to 4,500 lumens
- 3 individual light heads for task or area lighting
- 9 total output modes to manage output or run time
- Magnetic base, integrated hook, and screw holes for optimal surface mounting
- 270° horizontal rotation and 270° vertical articulation
- Integrated handles for easy carrying
- Highly durable and impact resistant design to withstand drops up to 2 m
- AC/DC versatility: Powered by MILWAUKEE® M18™ batteries, or mains plug supply
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Max. light output area mode high / medium / low (lumens)	4,500/ 2,000/ 1,200
Max. run time on area mode with M18 B5 battery (h)	3/ 6/ 11
Weight with battery pack (EPTA) (kg)	3.75 (M18 B5)
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933498149