

P125

Pocketherm Food Thermometer



Pocketherm is the latest pocket sized food thermometer from Comark. Aptly named, Pocketherm fits in a pocket, or a bag, and the probe is secured securely to the side of the thermometer, out of harm's way. Pocketherm switches on when the probe is swung away from the instrument and switches off when it is folded back. No buttons or adjustments required. The probe can be cleaned with a Comark bactericidal wipe between temperature checks.

- Probe swings open to switch on instrument
- Probe can be angled to suit usage
- Readings clearly shown on the large LCD display
- Thermistor accuracy meets all food hygiene regulations
- LEDs for error free indication of temperature zones
- Choice of models with either °C or °F display
- Auto switch off for even longer battery life
- Flashing LEDs for Instant Temperature Indication:-
 - Yellow for frozen
 - Green for chilled
 - Red for cooked

Sensor Type	Thermistor
Measurement Range	
P125	-40°C to +125°C
P125F	-40°F to +257°F
Scales	
P125	°C
P125F	°F
Displayed Resolution	0.1°
Accuracy at +23°C/+73°F (system)	
P125	±0.5°C, -20°C to +70°C
P125F	±0.9°F, -4°F to +158°F
Operating Range	
Temperature	-20°C/-4°F to +50°C/122°F
Humidity	10 to 90% non condensing
LED Indication (Flashing)	
Yellow	-18°C/0°F and below
Green	0°C/+32°F to +5°C/41°F inclusive
Red	+70°C/+158°F and above
	After 5 minutes

Auto Switch Off

After 5 minutes

Battery Type

PP3 9V

Battery Life

600 hours minimum (continuous)

Dimensions

Case L 170mm (probe retracted) x W 52mm x D 24mm
Probe L 110mm

Weight

140gms with battery