




---

 PRODUCT-DETAILS

# ASF28X3/T/BL

## INSP. T-PIECE PA66 28/28/28MM-BL




---

**General Information**

Extended Product Type	ASF28X3/T/BL
Product ID	7TCA296000R1709
EAN	5020963011726
Catalog Description	INSP. T-PIECE PA66 28/28/28MM-BL
Long Description	Adaptaseal Rotational Inspection T-Piece, Fine Profile, Nominal Conduit Size 28mm, Polyamide (Nylon) 66, Black

---

**Additional Information**

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Coupling Three Flexible Conduits in a T Configuration

---

**Ordering**

EAN	5020963011726
UPC	786210281636

---

## Technical

---

Number of Batteries	0
Color	Black
Material	Polyamide/Nylon 6.6

---



---

## Environmental

---

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---



---

## Container Information

---

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963011726

---



---

## Certificates and Declarations

---

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

---



---

## External Classifications and Standards

---

ETIM 8	EC001172 - Coupler for corrugated plastic hoses
ETIM 9	EC001172 - Coupler for corrugated plastic hoses
UNSPSC	39131717

---



---

## Categories

---

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

