

**ENGLISH** 

**Datasheet** 

Stock No: 113-4306

## Indicator, 8mm Panel Mount, Recessed, Red LED, Lead Pins Termination, 5 mm Lamp Size, 2 V





## **Product Details**

## LEDs with metal support, 34 type, board hole 8 mm

Brought to you under the trusted RS Brand, this LED indicator features a recessed lens behind a prominent bezel that not only protects the lens but offers a sixty degree angle of diffusion. Equipped with lead pins, this panel mounted indicator is easy to install, and has a robust nickel plated brass body.

- LED indicators for panel mounting.
- . The support is equipped with a standard 5 mm LED.
- · Supplied with nuts and washers.





## **Specifications**

Voltage Rating	2 V
Light Output Colour	Red
Mounting Hole Size	8mm
Lamp Size	5 mm
Length	17 mm
Туре	Panel Mount
Lamp Type	LED
Termination Type	Lead Pins
Bezel Style	Recessed
Bezel Colour	Chrome
Intensity	1.8 mcd
Current Rating	20 mA