



tesa® 64284

Product Information



Standard tensilised non-staining strapping tape

Product Description

tesa® 64284 is a medium duty tensilised polypropylene strapping tape with a natural rubber adhesive system.

tesa® 64284 is a specially designed tape which is stain and adhesive transfer resistant.

Application Fields

Closing, holding and securing in the appliance and furniture industry, reinforcing.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

• Backing material	MOPP	• Total thickness	115 µm
• Type of adhesive	synthetic rubber	• Colour	blue

Product Assortment

• Available Colours	white
---------------------	-------

Properties/Performance Values

• Elongation at break	35 %	• No discolouration	yes
• Tensile strength	300 N/cm	• Residue free removal	yes

Adhesion to Values

• steel	7 N/cm
---------	--------



tesa[®] 64284

Product Information

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=64284>