




**FETCHING AND GARDENING TAPS**

**Gardening taps + nose - brutto brass**

Brutto brass finishing.

Ref. code	Inlet	Ø nose	Ø pipe	Packaging
136900	3/8" NF 	1/2"	Ø12	1
136901	1/2"	1/2"	Ø12 (head 1/2")	1
136902	1/2"	1/2"	Ø12 (head 3/8")	1
136904	1/2"	3/4"	Ø15 (head 1/2")	1
136903	1/2" NF 	3/4"	Ø15 (head 1/2")	1
136906	3/4"	3/4"	Ø15 (head 1/2")	1
136905	3/4"	3/4"	Ø15 (head 3/4")	1
136907	3/4" NF 	1"	Ø20	1



ref. code 136903



ref. code 136904

MANIFOLDS

**SANITARY HOT WATER / HEATING TYP FC Ø 27 - SPACE 50 MM**

**Inlet Male 3/4" - Outlet Male 1/2" - End Female 3/4"**

Body Ø 27. Space 50 mm.  
Inside F1/2". Tested at 10 bar.

Ref. code	Description	Typ	Packaging
003682	2 outlets	Fc2	1
003683	3 outlets	Fc3	1
003684	4 outlets	Fc4	1
003685	5 outlets	Fc5	1
003686	6 outlets	Fc6	1
003687	7 outlets	Fc7	1
003688	8 outlets	Fc8	1
003689	9 outlets	Fc9	1
003690	10 outlets	Fc10	1
003691	11 outlets	Fc11	1
003692	12 outlets	Fc12	1



**Inlet Male 3/4" - Outlet Male 1/2" with glued valves - End Female 3/4"**

Body Ø 27. Space 50 mm. Inside F1/2".  
Glued valves outlet M1/2", with reversible proof hot water/cold water. Tested at 10 bar.

Ref. code	Description	Typ	Packaging
003633	2 outlets	Fc2	1
003634	3 outlets	Fc3	1
003635	4 outlets	Fc4	1
003636	5 outlets	Fc5	1
003637	6 outlets	Fc6	1
003638	7 outlets	Fc7	1
003653	8 outlets	Fc8	1
003654	9 outlets	Fc9	1



Reversible proof hot water / cold water

