

FEATURES

- **Nylon Material:** Provides excellent durability and resistance to wear and tear
- **55kg Tensile Strength:** Ensures secure fastening of cables and components
- **380mm Length:** Suitable for bundling large cable groups
- **Non-Releasable Design:** Offers a permanent and secure solution for cable management
- **UL 94 V-2 Fire Behaviour:** Meets fire safety standards for enhanced protection
- **RoHS Compliant:** Ensures adherence to environmental and safety regulations

RS PRO 380mm Nylon Cable Tie, 55kg Tensile Strength

RS Stock No: 656-012



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO offers a robust and reliable cable tie solution designed for securing and organising cables in various industrial settings. With a length of 380 mm, these non-releasable nylon cable ties provide a strong and durable option for managing cable bundles up to 105 mm in diameter. Ideal for high-temperature environments, they ensure stability and safety in demanding applications.

General Specifications

Colour	Light Brown
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	55 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	No

Mechanical Specifications

Length	380 mm
Material	Nylon
Maximum Bundle Diameter	105 mm
Width	7.6 mm

Operation Environment Specifications

Maximum Operating Temperature	150 °C
-------------------------------	--------

Approvals

Standards/Approvals	RoHS, UL94V-2
---------------------	---------------

