



ENGLISH

## Datasheet

Stock No: 235-938

# RS Pro Xenon Beacon, Flashing, Surface Mount, 12 V dc, 24 V dc



## Product Details

### Xenon Beacons, Single/Double Flash

Weatherproof and dustproof to IP56 these beacons offer high quality solutions for industrial environments and process applications.

Nominal flash output of 5J

Optional single or double flash

Approximately 80 flash per minute

High protection rating of IP56

Optional cage guard available

Surge protection for safety against peak voltage

Full internal suppression for maximum interference reduction

Operating temperature range: -30°C to +50°C

166mm diameter

Three point mounting

### Note

Lens must be purchased separately

Supplied with

Bulb



ENGLISH

## Specifications:

Supply Voltage	12 V dc, 24 V dc
Light Effect	Flashing
Lens Colour	Lens Not Included
Mounting Style	Surface Mount
Bulb Type	Xenon
Current Type	AC
Base Diameter	166mm
Housing Colour	Black
Lamp Included	Yes
Series	V10993
Height	207mm
Maximum Temperature	+50°C
Minimum Temperature	-30°C