



Microline Dot Matrix Printer

The no compromise, value for money 24-pin printer for demanding applications.

These compact and robust dot matrix printers not only produce great resolution output but also come with proven, class leading reliability. With USB fitted as standard, businesses can now enjoy greater flexibility and seamless connectivity, without having to compromise on price or performance.

Highlights:

- High quality resolution and definition
- 24-pin dot matrix for faster, sharper printing
- Suitable for more complex character requirements
- Up to 330 characters per second print speed
- High duty cycle and low maintenance means more productivity
- Fast and dependable with 10,000 hours MTBF
- Zero Tear Capability prevents waste
- USB as standard for even more flexibility

ML1190



The ML1190 dot matrix printer product specification

		ML1190
Order number		01196202
General	Number of pins	24
	No. of multi-part forms	5 (one original + 4 copies)
Speed & throughput	High speed draft (10 cpi)	333cps
	Utility (10 cpi)	250cps
	Letter quality (10cpi)	83cps
	Fastest print speed	333cps
Font & print features	Carriage width (10cpi)	80 columns
	Max. in compressed mode	160 columns
	Character pitch	10/12/15/17.1/20 pitch
	Graphics resolution	Up to 360 x 360 dpi
	Typeface & font	Courier (scalable), Roman (scalable), Swiss, Swiss Bold, Orator, Gothic, Prestige, OCR-A, OCR-B, Utility, HSD & Barcodes
	Typestyle	Emphasised, Enhanced, Double Width, Double Height, Italics, Outline, Shadow, Bold, Underline, Subscript, Superscript
Emulations & interfaces	Printer emulations	Epson LQ, IBM PPR or IBM AGM
	Standard interfaces	Centronics Parallel, USB 2.0, Serial RS232
	Optional interfaces	N/A
Paper handling	Continuous paper	76.2 - 254mm
	First printable line (from top of page)	Cut-sheet: 2.12mm (to centre of character), Continuous: 2.12mm (to centre of character)
	Standard	Automatic sheet loading, Short paper tear-off, Auto park feature
	Paper Feed	Top/Rear/Bottom path, Rear push tractor, top pull tractor, friction fed cut sheet
Physical	Dimensions (HxWxD)	150 x 349 x 232mm
	Weight	4.2kg
	Memory	64KB
	Noise level	51dBA(A) (ISO 7779)
Power	Power requirements	220V - 240V AC
	Frequency	50/60Hz
Reliability	Print head life	400M strokes/wire
	MTBF	10,000 hours
Warranty		3 years extended warranty upon registration within 30 days of purchase

Consumables

Only use genuine OKI Printing Solutions Original consumables to ensure the best quality and performance from your hardware. Non OKI Printing Solutions Original products may damage your printer's performance and invalidate your warranty.

Description	Life	Order Number
Ribbon	4 million characters	43571802



3-Year Return to Base Warranty

Our devices are manufactured to the highest standards of quality and technology, which has been confirmed by independent tests. We are so convinced of the high quality of our products that we are offering you an extension of the standard warranty period to 3 years at no extra cost to you. Simply register your product within 30 days of purchase to be eligible for our unique all inclusive offer. For further information please visit: www.oki.co.uk/warranty
Without registration, the standard pan-European 1 year return to base warranty applies.

OKI SYSTEMS (UK) LTD.
550 Dundee Road, Slough
Berkshire, SL1 4LE
United Kingdom
T +44(0) 1753 819819
F +44(0) 1753 819899
www.oki.co.uk

OKI

