

Previously known as: MICROCHEM® 4000 Oversleeves - Model 600

Engineered to provide an exceptional barrier against a wide range of organic and inorganic chemicals and biological agents..

DESIGN

A unique multi-layer barrier fabric renowned for its lightweight, yet robust textile feel and exceptional barrier to organic & inorganic chemicals.

ULTRASONICALLY WELDED SEAMS

Provides a strong liquid and particle barrier, made from the same fabric as the suit to maintain the same chemical resistance

SUIT FEATURES

- Elasticated at both ends
- Length 20"

COLOURS

Green

SIZES

One size



Industries

- Chemical
- Life Sciences
- Mining
- Fire and Rescue
- Oil and gas
- Automotive Aftermarket
- Food Processing

Applications

- Contaminated Environments
- Chemical Handling
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Opening and draining pumps valves or lines
- Loading and unloading of process equipment
- Raw material sample collection
- Concentration mixing and palletisation
- Hazmat response
- Assembly and disassembly of equipment


KEY FEATURES & BENEFITS

- Exceptional protection, over 200 chemicals permeation tested, including chemical warfare agents
- Designed to protect
- Silicone free


Technology



Material Diagram



Seam Diagram



Performance Standards


0598


EN 14126



EN ISO 13688:2013


PARTIAL BODY
PROTECTION ONLY


TYPE PB [3]


TYPE PB [4]

Product Information

Product Information	
Available Sizes	One Size
Color	Green
Country Of Origin	China
Packaging Overview	30 PR in a compressed bag
Product Material	Multi-layer non-woven barrier Laminate fabric
Product Reference	4000 Oversleeves - Model 600
Seam Type	Welded
Shelf Life	5 years

Suit components & accessories

Suit Components and Accessories	
Design Features	Elasticated at both ends and welded seams.

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

