

MODULE MOUSSE M3 CLIQUET – DOUILLES ¼ - 3/8 - ½ OGV GRIP®.

MODM.L1GRPPF



1/4"		ED 101T - 102T - 103T
		EH 103 - 104 - 105 - 106 - 107
		EP 101T - 102T - 103T
		ES 134.5T - 136.5T - 148T
		EXR 110 - 115 - 120 - 125 - 127 - 130 - 140
		ECR

							
1/4"	R.GRP. 5,5-6-7-8-9-10-11-12-13-14 mm	RL.161 R.180	EF.R180 - 100 mm R.209 - 55 mm R.210 - 100 mm	-	R.235	R.236CA	R.240A
	R.LA 6 - 7 - 8 - 9 - 10 mm						
1/2"	S.GRP 10 -11-12-13-14-15-16-17-18-19-21-22-24-27-30-32 mm	SXL.161	S.210A - 130 mm S.215 - 250 mm	S.120A	-		S.240A
	S.HLA 16-17-18-19-21 mm						
3/8"	J.H 8 - 9 -10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 -19 - 21 - 22 mm	JL.161	J.210 - 125 mm J.215 - 250 mm				J.240A
	J.HLA 11 - 12 - 13 - 14 - 15 mm						
		NSI.L 17-19-21 mm					

SKU	SKU Desc	EAN Code	RRP
MODM.L1GRPPF	MODULE MOUSSE M3 CLIQUET – DOUILLES ¼ - 3/8 - ½ OGV GRIP®.	3662424116667	€xx.xx