

Datasheet

RS Pro DC/DC Converter Isolated 24V to 12V 30A – Switch Mode

Stock number: 179-3350

RoHS 



Specifications:

Model	179-3350
Input voltage	24V
Output voltage	12V
Output current	30A
DC input voltage range	18-32V DC
Rated power	360W
Rated output voltage	DC 12V \pm 10%
Dimension(LxWxH)	157x91x47mm
N.W/unit	445g

Features:

- Anodized aluminum case provides durability & max heat dissipation
- The converter is compact, light weight and east to operate.
- 100% New components use
- 100% Real power
- Dual color LED indicate power & failure status
- Protections: over current, over voltage, overheat, short circuit.

