



Part Number : [731160027](#)

Product Description : MCRF Right-Angle Plug to Pigtail on 1.32mm Cable, 304.80mm Length, H25, 50 Ohms

Series Number : 73116

Status : Not Recommended For New Design

Product Category : RF Cable Assemblies



Documents & Resources

Drawings

[731160027_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	RF Cable Assemblies
Series	73116
Description	MCRF Right-Angle Plug to Pigtail on 1.32mm Cable, 304.80mm Length, H25, 50 Ohms
Application	RF
Assembly Configuration	Single Ended Connector
Connector to Connector	MCRF-to-Pigtail
Product Name	MCRF
Type	RF Cable Assembly
UPC	884982813564

Electrical

Frequency	6 GHz
Impedance	50Ω

Physical

Cable Length	304.80mm
Gender	Plug/Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Resin	Liquid Crystal Polymer
Packaging Type	Individual Bag
Single Ended	Yes
Wire/Cable Type	1.32mm Coaxial

Mates With / Use With

Mates with Part(s)

Description	Part Number
MCRF Jack, Straight, PCB	734120110

Receptacle, Surface Mount, 1.25mm Mounted Height, 50 Ohms	
MCRF Jack, Straight, PCB Receptacle, Surface Mount, 1.25mm Mounted Height, 50 Ohms	<u>734120114</u>
MCRF Cable Assemblies	<u>73412</u>

This document was generated on Nov 05, 2025