

F1.5-6VSC-H



Fork Terminal max 1.5SQMM M6



General Information

Extended Product Type	F1.5-6VSC-H
Product ID	7TBA301300R0115
EAN	5415022400465
Catalog Description	Fork Terminal max 1.5SQMM M6
Long Description	Vinyl-Insulated Fork Terminal, Single Crimp, Length 27mm, Width 12mm, Diameter 4.3mm, Stud Size M6, Wire Range 0.5-1.5mm ² , Copper, Tin Plated, Temperature Range -30 to 75 Degrees C, 600V Max, Color Red

Ordering

EAN	5415022400465
Minimum Order Quantity	2500 piece
Customs Tariff Number	8536904000

Dimensions

Product Net Weight	0.907 g
--------------------	---------

Container Information

Package Level 1 Width	25.4 mm
Package Level 1 Height	101.6 mm
Package Level 1 Depth / Length	152.4 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	152.4 mm
Package Level 2 Height	88.9 mm
Package Level 2 Depth / Length	177.8 mm
Package Level 3 Units	10000 piece
Package Level 3 Width	317.5 mm
Package Level 3 Height	203.2 mm
Package Level 3 Depth / Length	482.6 mm

Additional Information

Brand / Label	Spec-Kon
Color	Red

Material	Copper
Product Main Type	COMPRESSION TERMINALS
Product Name	Electrical Wiring Terminal
Product Type	Vinyl-Insulated Fork Terminal
UPC	786210135113

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	F1.5-6VSC-H
Instructions and Manuals	F1.5-6VSC-H

Classifications

ETIM 6	EC001052 - Solderless copper terminals for copper conductors
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

