

Features

- Waterproof IP67 rating guarantees protection against extended immersion under higher pressures
- Voltage rating of 125V AC/DC
- Current rating of 4A
- Gold-plated brass contacts for corrosion resistance
- Threaded mating type
- Operating temperature range from -25°C to 80°C
- Nickel plated brass shell

RS PRO Female M9 2 Pin Connector

RS Stock No.: 0132114



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

The 2 pin female M9 metal front mount socket connector had been widely used for automotive and sensor application, it's unshielded.

General Specifications

Number of Contacts	2
Shielding	unshielded
Housing Material	Brass
Contact Material	Phosphor copper
Contact Plating	Gold
Pole Format	2 pin
Contact Gender	Female
Mating Type	Threaded
Body Orientation	Straight
Mating Cycles	500
Typical conductor size	24AWG
Application	Sensor, automation

Electrical Specifications

Plug/Socket	Socket
Current Rating	4A
Voltage Rating	125V AC/DC
Insulation Resistance	$\geq 100M\Omega$

Mechanical Specifications

Connector Size	Standard
Termination Method	Solder
Mounting Type	Panel mount
Panel Cut-Out	$\varnothing 12.1\text{mm}$
Contact Diameter	24AWG

Operation Environment Specifications

Operating Temperature	-25°C to 80°C
-----------------------	---------------

Protection Category

IP Rating	IP67
-----------	------

Approvals

Compliance/Certifications	CE, RoHS, REACH, IP67
---------------------------	-----------------------