

# LED LENSER® X21.2

A large multi-LED hand torch producing such an awesome cannon of light that even some car headlights seem dim by comparison. Much favoured by emergency services personnel, search and rescue teams and subterranean activity enthusiasts this is a torch to be handled with care by only the very serious or professional user. Seven ultra-strong Xtreme Power LEDs inside its head can only mean one thing: shatteringly bright, mind-blowing brightness. In numeric terms that's 1600 lumens and 600 metres maximum penetrative strength. In actual terms this means it will light up the sides of mountains, the deepest of underground caves or further than the length of Brighton Pier. The patented Advanced Focus System optics and X-Lens Technology fuse the light rays into a circular, flawless close-range flood beam or a highly concentrated searchlight. It is simple to focus from one to the other by a forward and back Speed Focus on the head of the torch. A push switch on the barrel allows the user to adjust consumption settings from Low Power to Power to Defence Strobe. The X21.2 has a stunning burn time up to 100 hours on Low (250 lumens) and is supplied with 4 x D-batteries plus a protective hard case and comfortable detachable shoulder strap.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Seven LED super bright large hand-held light cannon with stunning lighting performance
- Energy efficient CREE® Xtreme+ LED Light Chips
- State-of-the-art, reliable German engineering
- Advanced Focus System™ Optics. Patented reflector and lens combination for intense spot (distance ) or flawless flood (near ) illumination
- X-Lens Technology™. Multiple lenses perfectly calibrated to produce an awesome single beam
- Smart Light Technology™. Micro-chip controlled light options -Power, Low Power, Defence Strobe
- Speed Focus™ . Instant, smooth, stage-less beam selection.
- Dynamic Switch™ - Reactive, single switch control
- Large beam width due to larger head size – great for illuminating large areas
- Robust, protective aircraft-grade aluminium housing
- User-friendly modular design
- Corrosion resistant gold plated contacts for better conductivity
- Water and dust resistant. IPX54
- Protective hard carry/storage case

## Technical Information

Size: 397 x 95mm Ø

Power: 1600 lumens max

Run Time: up to 100 hours

Beam Distance: up to 600m

Weight: 1400grams

Supplied with : Hard Case, Shoulder-strap, and Duracell® batteries (4xD)

Code	Colour	Packaging	Barcode
9421	Black	Hard Case	4029113942133