

PRODUCT-DETAILS

# ULNY-018-8-C

## CABLE CLAMP 3.1IN GRAY NYL LADDER



### General Information

Extended Product Type	ULNY-018-8-C
Product ID	7TAG009970R0155
EAN	5414363068815
Catalog Description	CABLE CLAMP 3.1IN GRAY NYL LADDER
Long Description	Adjustable Ladder-Style Cable Clamp, Gray Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 79.4mm (3.12 Inches), Width of 12.0mm (0.472 Inches), Self-Adhesive Mounting, Optional Screw Hole Diameter of 2.79mm (0.110 Inches) for #4 or #5 Flat Head Screw

### Ordering

EAN	5414363068815
UPC	728494087092

### Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	8.38 in 213 mm
Package Level 1 Height	2.25 in 57 mm
Package Level 1 Depth / Length	2.25 in 57 mm
Package Level 2 Units	1000 piece
Package Level 2 Width	13.2 in

	335 mm
Package Level 2 Height	10.7 in
	272 mm
Package Level 2 Depth / Length	17.2 in
	437 mm

**Additional Information**

Brand / Label	Ty-Rap
Color	Gray
Effective Date	19960215
Material	Nylon/Polyamide 6.6
Mounting Type	Rubber-Based Adhesive
Number of Batteries	0
Product Name	AJUSTABLE CABLE CLAMPS
Product Type	Adjustable/Ladder Cable Clamps
Special Functions	Ladder-style fastener is easily released and refastened.

**Certificates and Declarations (Document Number)**

Data Sheet, Technical Information	ULNY-018-8-C
Instructions and Manuals	ULNY-018-8-C

**Classifications**

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121705
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5049 >> Cable clamp and staple

**Categories**

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

