



GBC Inspire+ A4 Laminator

Lightweight and compact, the Inspire+ A4 Laminator is perfect for the occasional home or office user with basic requirements. It is really simple to operate via a single switch, warms up in 5 minutes and takes standard 2x75 micron pouches. It handles items from ID to A4 size while the exit tray ensures a perfectly flat finish. Get creative with the Inspire+ - imagination is all you need!



Attributes

- A4 laminator
- Warms up in 5 minutes
- Uses 2x75 micron pouches
- Laminates from ID to A4 size
- Cold setting for use with self-adhesive cold seal pouches
- For best results use with GBC document pouches

Specifications

Number	4402075
Colour	black
Dimensions (W x H x D)	350 x 60 x 130 mm
Laminating Speed (mm/min)	250
Power Supply	220/240 V AC
Warm up Time (min)	4
Heating System	2 heated rollers
Operation Mode	2 roller, no carrier, temperature controlled
Max. Laminating Width (mm)	241
Max. Laminating Thickness (mm)	0.5
Max. Pouch Thickness (microns)	75
Power Consumption (W)	450
Dimensions (with Tray) mm	350(W) x 60(H) x 125(D)
Anti-Jam Technology	Manual Release
Approx. lamination time (A4)	72 secs (A4 75 microns)
Photo friendly	Yes
Type	Pouch
Weight	1300 g
Pallet quantity	180
EAN code	5028252502702