

Technical data sheet

Article number:
924-00527

2R10

Product Group	Ring Terminals
Product Family	Single Grip Pre-Insulated
Material	Copper (CU), Polyvinylchloride (PVC)
Colour	Blue (BU)
Application Range	Low Voltage
Conductor Size Range mm ²	1.5-2.5 mm ²
Diameter (D)	4.7 mm
for Hole Ø (FH)	10.5 mm
Length (L)	31.4 mm
Length (L2)	10.7 mm
Length (L3)	20.7 mm
Max Current	27 A
Max Voltage	600 V
Operating Temperature	+75 °C
Package Content	50 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	13.7 mm

RoHS 