

Datasheet

RS Pro D-sub Connector Backshell

RS Stock No: **544-4405A**



Product Details

RS Pro D-sub connector backshell is suitable for use with most standard and crimp D connector. It has a cover in black moulded noryl to UL94V-0 specification. This connector backshell offers locking action with jack screws in combination with female screwlock assembly. The backshell provides side and top cable entry through a removable knockouts and cable retention. The connector backshell features 37 contacts.

Features and Benefits

- Cable to panel adapter system suitable for use with most standard and crimp D connectors
- Cover in black moulded Noryl to UL94V-0
- Offers locking action with jack screws in combination with female screwlock assembly
- Side or top cable entry via removable knockouts and cable retention
- Temperature of -20 to +75°C



ENGLISH

Specifications:

Body Orientation	Straight
Colour	Black
Housing Material	PET
Number of Contacts	37
Dimensions	53.1 x 73 x 16.3 mm
Operating Temperature Range	-20 to +75°C
Standards Met	UL 94V-0