



MINI 15-PP10

Blade Fuse, Mini, 15A, Blue

Product Properties:

Release characteristic	Fast (F)
Rated voltage	32 V
Type of current	DC
Colour code	Blue
Nominal voltage DC	58 V
Number of fuses	10 .
Model	Blade fuse
Max. current (I _{max})	15 A
Nominal current	15 A
Fuse type	Mini

Dimensions:

Width	11 mm
MOQ	10 .
Unit	pck
Rated voltage	32 V
Length	16.2 mm

Approvals:

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

Other information:

ETIM-Class	EC002298 - Blade fuse
ETIM-Release	9.0
Trademark	NECORE
Product Group	Blade fuses - Pin-pac
Search Description	FLATSÄKRING, MINI, 15A
Alternative SKU	MINI15-PP10

Logistic information:

Barcode	733117618646
Country of origin	TW
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	10 .
Stock code	MINI 15-PP10
Taric code	85361050
Unit	pck

*We reserve the right to make technical changes and disclaim any typographical errors.