

## FEATURES

- **Sintered Bronze Material:** Provides high wear resistance and longevity
- **Flanged Design:** Ensures secure positioning and easy installation
- **Dynamic Load Rating of 14 N/mm<sup>2</sup>:** Suitable for applications with varying load conditions
- **Static Load Rating of 50 N/mm<sup>2</sup>:** Capable of handling significant static loads
- **Outside Diameter of 21.05 mm:** Fits standard housings for easy integration

## RS PRO 15.02 mm Flanged Plain Bearing

RS Stock No: 529-035



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient rotational movement. Made from sintered bronze, it offers excellent durability and performance in various industrial settings. The bearing's primary benefit is its ability to support both dynamic and static loads effectively, making it ideal for machinery and equipment that require smooth operation.

## General Specifications

Bore Size	15.02 mm
Dynamic Load Rating	14 N/mm <sup>2</sup>
Product Type	Plain Bearing
Static Load Rating	50 N/mm <sup>2</sup>
Sub Type	Flanged

## Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	21.05 mm
Width	20 mm

## Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

