



## Main

Range	Thalassa
Product name	Thalassa PLA
Enclosure type	Multi-purpose
Product or component type	Suitable enclosure
Version	PLA
Nominal height	2000 mm
Nominal width	750 mm
Nominal depth	420 mm
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 2 side part 1 rear panel 2 door

## Complementary

Body type	Sealed top and bottom part assembled with side parts
Door type	Plain front
Number of doors	2 door(s)
Door opening side	Reversible (120 °)
Lock type	4 points lock, 5 mm double-bar
Accessibility for operation	Rear Front
Removable parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	UL 508 A IEC 62208
NEMA degree of protection	NEMA 12 NEMA 3X NEMA 2 NEMA 5 NEMA 13 NEMA 3R NEMA 3 NEMA 3S NEMA 1
Product certifications	DNV Marine Veritas UL/cUL listed

## Environment

IP degree of protection	IP65 conforming to IEC 60529 (completely sealed)
IK degree of protection	IK10 conforming to IEC 62262 (plain door)
Fire resistance	960 °C conforming to IEC 62208
Ambient air temperature for storage	-35...90 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>