



## 18V XR Pole Hedge Trimmer – 1x 5.0Ah

DCMPH566P1-QW

**POWER** – Quick and efficient cut. Blade-cut capacity = 25mm, 2800 spm.  
**REACH/ANGLES** – 3.35m max. reach 7° position, 180°, articulating head  
3.35m max reach (based on a 1.80m person holding the pole in a  
straightened position at chest level)

**ERGONOMICS** – Lightweight and manouvrable. Well balanced

**RUNTIME** – Up to 75 min of runtime with a 5Ah battery.



Maximum working width	550
-----------------------	-----

Blade Length	550 mm
--------------	--------

Sound Power Uncertainty	81.599999999999994 dB(A)
-------------------------	--------------------------

Battery Capacity	5 Ah
------------------	------

Battery Type	Lithium-Ion
--------------	-------------

Battery Voltage	18 V
-----------------	------