


## FEATURES

- **IP66 Rating:** Offers excellent protection against dust and water, suitable for harsh environments
- **200W Maximum Output Power:** Supports high-power LED lighting systems
- **12V Output Voltage:** Provides a stable voltage for LED applications
- **16.6 A Driver Current:** Ensures efficient power delivery to connected devices
- **Multiple Dimming Operations:** Compatible with Leading Edge, PWM, and Trailing Edge dimming for flexible lighting control
- **Constant Voltage Operation:** Maintains consistent voltage output for reliable LED performance
- **Wide Input Voltage Range (200-240 V AC):** Compatible with standard AC power supplies

## RS PRO 200W LED Driver, IP66 12V

RS Stock No: 642-792



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO 200W LED Driver is designed to provide reliable power for LED lighting systems. With a robust IP66 rating, it is ideal for outdoor and industrial environments where protection against dust and water is essential. This constant voltage LED driver ensures consistent performance, making it suitable for a variety of lighting applications.

### General Specifications

Dimming Operation	Leading Edge, PWM, Trailing Edge
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

### Electrical Specifications

Driver Current	16.6 A
Input Voltage	200-240 V ac
Input Voltage Type	AC
Maximum Output Power	200 W
Output Voltage	12 V

### Protection Category

IP Rating	IP66
-----------	------

### Approvals

Standards/Approvals	CE, EN55015, EN61000-3-2, 3, EN61000-4-2,3,4,5,6,11, EN61347-1, EN61347-2-13, EN61547
---------------------	---