



Easy Rack 600mm/42U/800mm with Roof, Side panel, castors, feet and 4 Brackets, No Bottom, black

ER6282

Overview

Lead time Usually in Stock

Main

Product or component type	Rack	
Number of rack unit	42U	
Provided equipment	Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters	
	Side panels	

Physical

Height	199.1 cm	
Width	60 cm	
Depth	80 cm	
Net weight	94.4 kg	
Colour	Black	
Mounting mode	Not rack-mountable	
Maximum mounting depth	64.14 cm	
minimum mounting depth	19.05 cm	
Rack width	19"	
Marking	18 gauge front door 19 gauge rear door 16 gauge post 14 gauge EIA mounting rail	
Permanent permissible load	1199.8 kg static 599.6 kg dynamic	

Conformance

 Standards
 UL 2416

 UL 60950-1
 EIA-310E

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	4

Package 1 Height	212 cm	
Package 1 Width	85 cm	
Package 1 Length	65 cm	
Package 1 Weight	100 kg	
Pallet layers	1	

Contractual warranty

Warranty 5 year repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint		
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	303	

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No