



Make the switch

1 Gang 13A DP Switched Socket - Georgian Brass, White Insert + Metal Rocker

Stock code: 3346GBWM



Technical

Associated standards:	BS 1363-2
Ambient operating temperature:	-5 to 40°C (24hour average not exceeding 25°C)
Base material:	Thermoset
Face plate material:	brass
Fixing screws:	2 x M3.5
IP rating:	IP2X
Maximum installation altitude:	2000m
Minimum switch contact gap:	3 mm
Minimum wall box depth:	25
Nature of supply:	AC
Operational testing:	30000
Rated current:	13A
Rated frequency:	50-60Hz
Rated voltage:	220-250V
Switched poles:	2 pole
Terminal capacity:	3 x 2.5mm 3 x 4.0mm 2 x 6.0mm

General

Face plate finish:	polished brass
Insert colour:	white
Number of outlets:	1
Rocker finish:	polished brass
Switched:	Yes

Technical: +44 (0) 208 208 7414 Sales: +44 (0) 208 208 7419 E-mail: sales@contactum.co.uk