

Specifications for BMP41/BMP51/BMP53 Labelmaker Labels

| | |
|-------------------------------------|---|
| Adhesive | Permanent Acrylic |
| Article No. | 131588 |
| Brady Material No. | B-499 |
| Material Type | Nylon Cloth |
| Colour | Black on White |
| Finish | Matt |
| Order Reference | M-141-499 |
| Printable Area - Height (mm) | 25.40 |
| Printer Compatibility | BMP41; BMP51; BMP53 |
| Size - Height (mm) | 57.15 |
| Size - Width (mm) | 25.40 |
| Additional Information | Approx. 25.40 mm x 25.40 mm resulting flag size |
| Thickness (mm) | 0.166 |
| Total Qty per Pack | 90 Label(s) / Box |
| Approval/Compliance | UL Recognised; CSA Accepted; Halogen Free (DIN VDE 0472/part 815) |
| Adhesive (Y/N) | Yes |
| Application | Voice & Data Communication |
| Environment | Freezer; Liquid Nitrogen; Autoclave |
| Industry | Data & Telecommunications; Electrical |
| Max. Service Temp. °C | 90 |
| Min. Service Temp. °C | -40 |
| Shape | Rectangle |
| Software | LabelMark |
| Surface | For smooth, textured/rough or Highly textured/Low surface energy surfaces |
| Voice/Data Application | Cable Flags |