

Dell EMC AOC-SFP-10G-5M Compatible 5m/16.4ft 10G SFP+ to SFP+ AOC Cable - 10GbE SFP+ Active Optical Fiber - 10Gbps SFP Plus/Mini GBIC/Transceiver Module Cable -

**Product ID:** AOCSFP10G5ME



The AOCSFP10G5ME is a Dell EMC AOC-SFP-10G-5M compatible fiber optical SFP+ cable that is designed, programmed and tested to work with Dell EMC brand 10 Gb compatible servers or routers and complies with MSA industry standards.

This active optical SFP+ cable (AOC) supports 10GbE applications connected through SFP+ (Mini-GBIC) ports and is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions. The AOC cable is lighter and more flexible than SFP+ direct-attach cables which makes it ideal for installation in tight spaces and over longer distances.

Designed for high-speed interconnects, this low-power, low-latency optical cable is ideal for applications such as point-to-point in-rack and across-rack network switch or server connections.

All StarTech.com SFP & SFP+ cables are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of direct-attach SFP cables and SFP modules, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility



## Applications

## Features

- **Dell EMC AOC-SFP-10G-5M COMPATIBLE ACTIVE OPTICAL CABLE (AOC):** Works with Dell EMC switches like , and others
- **TECHNICAL SPECS:** 5m Active Optical Cable 10Gbps Active Optical Fiber 2x SFP+ Pluggable Connector PVC Cable Jacket Hot swappable MSA Compliant
- **DESIGNED FOR SERVER ROOMS:** A convenient alternative to transceivers inside and between racks. Factory termination means high performance & reliability, with less maintenance
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance

---

#### Hardware

Warranty	Lifetime
Compatible Brand	Dell EMC
Cable Type	Active Optical Cable

---

#### Performance

Maximum Data Transfer Rate	10.00 Gbps
Wavelength	850nm
Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	10 Gbps
MTBF	19,083,969 hours
Power Consumption (In Watts)	< 1.2W

---

#### Connector(s)

Connector A	1 - SFP+
Connector B	1 - SFP+

---

#### Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 85C (-4F to 185F)

Humidity	0~85% RH
----------	----------

---

**Physical Characteristics**

Product Length	196.8 in [500.0 cm]
Product Width	0.6 in [1.4 cm]
Product Height	0.5 in [1.2 cm]
Weight of Product	11.4 oz [323 g]

---

**Packaging Information**

Package Length	7.2 in [18.2 cm]
Package Width	6.5 in [16.6 cm]
Package Height	1.3 in [3.2 cm]
Shipping (Package) Weight	3.8 oz [108.0 g]

---

**What's in the Box**

Included in Package	1 - SFP+ Cable
---------------------	----------------

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*